




TIME DIVISION MULTIPLEXING/ DEMULTIPLEXING TRAINER MODEL- COM109Z

This trainer has been designed with a view to provide practical and experimental knowledge of 4 channel Time Division Multiplexing Demultiplexing using PAM technique on a SINGLE P.C.B of size 15"x 12".



SPECIFICATIONS

1. Power supply requirement : 230V AC, 50 Hz.
2. Built in IC based power supply.
3. On Board four Input signals generators.
 1. Sine wave : Frequency 250 Hz.- 2 Vpp
 2. Sine wave : Frequency 500 Hz.- 2 Vpp
 3. Sine wave : Frequency 1K Hz.- 2 Vpp.
 4. Sine wave : Frequency 2K Hz.- 2 Vpp
4. On Board Sampling Pulse signal generator.
Frequency Range : 2 KHz to 64 KHz.
5. Modulator Sections : Multiplexer
6. Demodulator Sections : Demultiplexer & Low Pass Filter
7. Built-in Gaussian Noise Generation and Matched Filter
8. The parts soldered on the front side of SINGLE PCB with complete circuit diagram screen printed.
9. Standard Accessories :
 1. A Training Manual.
 2. Connecting Patch cords.

In keeping view of SIGMA policy of continuous development and improvement, the Specifications may be changed without prior notice or obligation.

Sigma Trainers and Kits
E-113, Jai Ambe Nagar,
Near Udgam School,
Thaltej,
AHMEDABAD - 380054.
INDIA.

Phone(O): +91-79-26852427/ 26850829
Phone(F): +91-79-26767512/ 26767648
Fax : +91-79-26840290/ 26840290
Mobile : +91-9824001168
Email : sales@sigmatrainers.com
: sigmatrainers@sify.com
Web : www.sigmatrainers.com

Dealer:-