



# PRESSURE AMPLIFIER

## MODEL PAMP100

This board has been designed with a view to provide practical and experimental knowledge of Pressure Amplifier.

### SPECIFICATIONS

1. Input Pin Connection Details : 9 Pin male connector
2. Out Put Pin Connection Details : 9 pin female connector
3. Output Voltage : 1 V per 100mmHg
4. Max. input pressure : 250mmHg
5. Input Impedance : 5MOhms
6. Excitation Voltage : 5V
7. Enclosure : ABS

In keeping view of SIGMA policy of continuous development and improvement, the Specifications may be changed without prior notice or obligation.

**Sigma Trainers and Kits**  
E-113, Jai Ambe Nagar,  
Near Udgam School,  
Thaltej,  
AHMEDABAD - 380054.  
INDIA.

**Phone(O): +91-79-26852427/ 26850829**  
**Phone(F): +91-79-26767512/ 26767648**  
**Fax : +91-79-26840290/ 26840290**  
**Mobile : +91-9824001168**  
**Email : sales@sigmatrainers.com**  
**: sigmatrainers@sify.com**  
**Web : www.sigmatrainers.com**

**Dealer:-**